

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 2050AB-01

Images



Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Delivered:	With certificate of inspection, bezel clamp
Range:	20 mm
Range per rev.:	1 mm
Dial reading:	$\pm 0-100$
Graduation:	0,01 mm
MPE first one revolution:	$\pm 10 \mu\text{m}$
MPE first 2 1/2 revolutions:	$\pm 10 \mu\text{m}$
MPE > 2 1/2-10 revolutions:	$\pm 15 \mu\text{m}$
MPE > 10-20 revolutions:	$\pm 20 \mu\text{m}$
H MPE (Hysteresis):	$4 \mu\text{m}$
R MPE (Repeatability):	$\pm 3 \mu\text{m}$
Type:	ANSI/AGD Standard
Measuring force:	0,4-2 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF

Accessories

Optional accessories:	
------------------------------	--



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application

Spindle Lifting Lever

for S and A-Type Serie 2,3 >10/0,4" up to 20mm/0,8"

Art No. 21AZB150

Price on application



Standard accessories:



Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 2.10 €*

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 15.00 €*

