


Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 2056A-01

Images



Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	25 mm
Range per rev.:	1 mm
Dial reading:	±0-100
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0,01 mm
MPE first one revolution:	±10 µm
MPE first 2 1/2 revolutions:	±10 µm
MPE > 2 1/2-10 revolutions:	±15 µm
MPE > 10-20 revolutions:	±20 µm
MPE > 20 revolutions:	±25 µm
H MPE (Hysteresis):	4 µm
R MPE (Repeatability):	±3 µm
Type:	ANSI/AGD Standard
Measuring force:	0,4-2,5 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*