

Dial Gauge, Lug Back, ANSI/AGD Type

Item number: 2414A

Images



ANSI/AGD Type Unit: in

Code No.	A	B	C	D	E	F	G	H	I	Mass (g)
2414A	1.53	2.52	2.24	0.71	3/4	0.54	0.87	2.05	0.30	164
2415A	1.53	2.52	2.24	0.71	3/4	0.54	0.87	2.05	0.30	164
2514A	1.53	2.52	2.24	0.71	3/4	0.54	0.87	2.05	0.30	164
2506A	1.86	2.14	2.24	0.71	3/4	0.54	0.48	2.05	0.30	164
2507A	1.86	2.14	2.24	0.71	3/4	0.54	0.48	2.05	0.30	164
2514A	1.53	2.52	2.24	0.71	3/4	0.54	0.87	2.05	0.30	164
2922A	1.86	2.14	2.24	0.71	3/4	0.54	0.48	2.05	0.30	164
2356A-10	1.86	2.26	2.24	0.71	3/4	0.54	0.59	2.05	0.30	163
2358A-10	1.53	2.50	2.24	0.71	3/4	0.54	0.85	2.05	0.30	164
2802A-10	1.86	2.02	2.24	0.71	3/4	0.54	0.37	2.05	0.30	164
2803A-10	1.86	2.02	2.24	0.71	3/4	0.54	0.37	2.05	0.30	164
2804A-10	1.86	2.04	2.24	0.71	3/4	0.54	0.38	2.05	0.30	166
2805A-10	1.86	2.04	2.24	0.71	3/4	0.54	0.38	2.05	0.30	166
2806A-10	1.86	2.04	2.24	0.71	3/4	0.54	0.38	2.05	0.30	164
2923A-10	1.86	2.04	2.24	0.71	3/4	0.54	0.38	2.05	0.30	164



Description

Standard Type, 0,5" / 0,125" Range, 0,001" / 0,005" Graduation - Inch

This is a standard, inch dial indicator. It offers you the following benefits:


- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed and removed without tools.
- No through screw holes on the frame and secure adhesion between the bezel and the crystal as well as the use of an O-ring prevents water or oil penetration.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0,5 "
Range per rev.:	0,1"
Dial reading:	±0-100
Delivered:	With certificate of inspection, bezel clamp

Graduation:	0,001"
H MPE (Hysteresis):	0,0002"
R MPE (Repeatability):	±0,0002"
MPE first one revolution:	±0.001"
MPE first 2 1/2 revolutions:	±0,001"
MPE > 2 1/2-10 revolutions:	±0,001"
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,8 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Continuous dial:	Yes
Mass:	164 g

Dimensions



A: 1.53 inch

B: 2.52 inch

C: 2.24 inch

D: 0.71 inch

E: 3/4 inch

F: 0.54 inch

G: 0.87 inch

H: 2.05 inch

I: 0.3 inch

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application

Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application



Standard accessories:

Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*
Photo Not Available



Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*
