

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 2109A-11

Images



Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Delivered:	With certificate of inspection, bezel clamp
Range:	1 mm
Range per rev.:	0,2 mm
Dial reading:	0-10-0
Graduation:	0,001 mm
MPE first one revolution:	$\pm 3 \mu\text{m}$
MPE first 2 1/2 revolutions:	$\pm 3 \mu\text{m}$
MPE > 2 1/2-10 revolutions:	$\pm 4 \mu\text{m}$
H MPE (Hysteresis):	$2 \mu\text{m}$
R MPE (Repeatability):	$\pm 0.3 \mu\text{m}$
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,5 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application

Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application



Standard accessories:

Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 2.10 €*



Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 15.00 €*
