


## Dial Gauge, Lug Back, ISO Type

Item number: 2118A-10

### Images



### Description

#### Standard Type, 2 and 5 mm Range, 0.001 / 0.005 mm Graduation

This is a standard dial indicator. It offers you the following benefits:


- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed and removed without tools.
- No through screw holes on the frame and secure adhesion between the bezel and the crystal as well as the use of an O-ring prevents water or oil penetration.

### Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Metric
<b>Type:</b>	EN ISO Standard
<b>Delivered:</b>	With certificate of inspection
<b>Range:</b>	5 mm
<b>Range per rev.:</b>	0,2 mm

<b>Dial reading:</b>	0-100-100
<b>Graduation:</b>	0.001 mm
<b>MPE any 1/10 revolution:</b>	4 μm
<b>MPE any 1/2 revolution:</b>	6 μm
<b>MPE any 1 revolution:</b>	6.5 μm
<b>MPE measuring range:</b>	10 μm
<b>H MPE (Hysteresis):</b>	2.5 μm
<b>R MPE (Repeatability):</b>	2 μm
<b>Measuring force:</b>	0,4-1,5 N
<b>Mass:</b>	146 g
<b>Stem:</b>	8 mm
<b>Contact point:</b>	Carbide tipped, thread: M 2.5 x 0.45 mm
<b>Continuous dial:</b>	Yes

## Dimensions



**A:** 47,2 mm

**B:** 60.7 mm

**C:** 57 mm

**D:** 18.1 mm

**E:** 20 mm

**F:** 16.9 mm

**G:** 15.3 mm

**H:** 52 mm

**I:** 7.6 mm

## Accessories

Optional accessories:



### Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



## Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

[Price on application](#)

## Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator  
Serie 2/3/4

Art No. 21EZA198

[Price on application](#)



## Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

[Price on application](#)



## Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

[Price on application](#)



## Spare parts

Consumable spares:



## Contact Element Ball Point, M2,5x0,45

7,3mm Length, Carbide, Metric

Art No. 901312

Suggested retail price: 14.00 €\*  

---