


Dial Gauge, Flat Back, ISO Type

Item number: 2118AB-10

Images



Description

Standard Type, 2 and 5 mm Range, 0.001 / 0.005 mm Graduation


- This is a standard dial indicator. It offers you the following benefits:
- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed and removed without tools.
 - No through screw holes on the frame and secure adhesion between the bezel and the crystal as well as the use of an O-ring prevents water or oil penetration.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Type:	EN ISO Standard
Range:	5 mm
Range per rev.:	0,2 mm
Dial reading:	0-100-100

Delivered:	With certificate of inspection
Graduation:	0.001 mm
MPE any 1/10 revolution:	4 µm
MPE any 1/2 revolution:	6 µm
MPE any 1 revolution:	6.5 µm
MPE measuring range:	10 µm
H MPE (Hysteresis):	2.5 µm
R MPE (Repeatability):	2 µm
Measuring force:	0,4-1,5 N
Stem:	8 mm
Contact point:	Carbide tipped, thread: M 2.5 x 0.45 mm
Continuous dial:	Yes
Mass:	137 g

Dimensions



A: 47,2 mm

B: 60.7 mm

C: 57 mm

D: 18.1 mm

E: 20 mm

F: 16.9 mm

G: 15.3 mm

H: 52 mm

I: 7.6 mm

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application

Spare parts

Consumable spares:



Contact Element Ball Point, M2,5x0,45

7,3mm Length, Carbide, Metric

Art No. 901312

Suggested retail price: 5.00 €*
