



Dial Gauge, Lug Back, ISO Type

Item number: 2928A

Images



Description

Graduation 0.01 / 0.1 mm

- This is a one revolution dial indicator. It offers you the following benefits:
- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed without tools.
 - No through screw holes on the frame and secure adhesion between the bezel and the crystal as well as the use of an O-ring prevents water or oil penetration.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Type:	EN ISO Standard
Range:	4 mm
Plunger Stroke:	10 mm
Range per rev.:	5 mm

Dial reading:	2-0-2
Delivered:	With certificate of inspection
Graduation:	0.1 mm
MPE any 1/10 revolution:	15 µm
MPE measuring range:	25 µm
H MPE (Hysteresis):	12 µm
R MPE (Repeatability):	20 µm
Measuring force:	0,4-1,4 N
Stem:	8 mm
Contact point:	Carbide tipped, thread: M 2.5 x 0.45 mm
One revolution:	Yes
Shockproof:	Yes
Mass:	145 g

Dimensions

A: 47.2 mm

B: 65.2 mm

C: 57 mm

D: 18.1 mm

E: 20 mm

F: 16.9 mm

G: 19.8 mm

H: 52 mm

I: 7.6 mm

Accessories

Optional accessories:

Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application



Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application

Spare parts

Consumable spares:



Contact Element Ball Point, M2,5x0,45

7,3mm Length, Carbide, Metric

Art No. 901312

Suggested retail price: 5.00 €*
