

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 2424AB-19

Images



Description

This is a standard, inch dial indicator. It offers you the following benefits:

- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed and removed without tools.
- No through screw holes on the frame and secure adhesion between the bezel and the crystal as well as the use of an O-ring prevents water or oil penetration.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	2 "
Range per rev.:	0,1"
Dial reading:	±0-100
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0,001"
H MPE (Hysteresis):	0,00033"
R MPE (Repeatability):	±0,0002"
MPE first one revolution:	±0,001"
MPE first 2 1/2 revolutions:	±0,001"
MPE > 2 1/2-10 revolutions:	±0,002"
MPE > 10-20 revolutions:	±0,003"

Type:	ANSI/AGD Standard
Measuring force:	0,4-2,5 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Continuous dial:	Yes
Coaxial revolution counter:	Yes
Cushioned end point:	Yes
Shockproof:	Yes
Mass:	225 g

Dimensions

A: 4.65 inch
B: 5.61 inch
C: 2.24 inch
D: 0.71 inch
E: 5/6 inch
F: 2.14 inch
G: 2.35 inch
H: 2.05 inch
I: 0.37 inch

Accessories

Optional accessories:

Limit Hands (green) 2pcs
Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application

Standard accessories:


Bezel Clamp for Dial Gauge

Inch, Series 2/3/4
Art No. 21RZA065
Suggested retail price: 5.00 €*



Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch
Art No. 21BZB056
Suggested retail price: 8.30 €*
