


Dial Gauge, Lug Back, ISO Type

Item number: 2901A-10

Images



Description

Graduation 0.001 mm

This is a one revolution dial indicator. It offers you the following benefits:

- Bezel clamp and lifting lever (optional) can be attached to either right or left side.
- No through screw holes on the frame as well as the use of an O-ring prevents water or oil penetration.
- It eliminates the possibility of reading errors due to miscounting multiple revolutions.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Type:	EN ISO Standard
Delivered:	With certificate of inspection
Range:	0.16 mm
Plunger Stroke:	4.1 mm

Range per rev.:	0,2 mm
Dial reading:	80-0-80
Graduation:	0.001 mm
MPE any 1/10 revolution:	2 µm
MPE measuring range:	4 µm
H MPE (Hysteresis):	2 µm
R MPE (Repeatability):	1 µm
Measuring force:	0,4-1,5 N
Mass:	149 g
Stem:	8 mm
Contact point:	Carbide tipped, thread: M 2.5 x 0.45 mm
One revolution:	Yes
Shockproof:	Yes

Dimensions

A: 47.2 mm
B: 66.1 mm
C: 57 mm
D: 18.1 mm
E: 20 mm
F: 16.9 mm
G: 20.7 mm
H: 52 mm
I: 7.6 mm

Accessories

Optional accessories:

Limit Hands (green) 2pcs
Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application



Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

[Price on application](#)

Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

[Price on application](#)



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

[Price on application](#)



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

[Price on application](#)



Spare parts

Consumable spares:



**Contact Element Ball Point,
M2,5x0,45**

7,3mm Length, Carbide, Metric

Art No. 901312

Suggested retail price: 14.00 €*
