


Dial Gauge, Lug Back, ANSI/AGD Type

Item number: 2909A-62

Images



Description

One Revolution Type for Error-free Reading


- Light weight type / standard type
- Limiting pointer rotation to one revolution eliminates the reading errors that can occur with dial indicators featuring more than one revolution of the pointer for full stroke.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0,04 "
Plunger Stroke:	1.9 mm
Range per rev.:	0.05"
Dial reading:	20-0-20
Delivered:	with certificate of inspection
Graduation:	0.0005"
H MPE (Hysteresis):	0,00016"

R MPE (Repeatability):	±0,0001"
MPE first one revolution:	±0,0005"
Type:	ANSI/AGD Standard
Measuring force:	0,4-2,5 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
One revolution:	Yes
Cushioned end point:	Yes
Mass:	163 g


Dimensions




A: 1.86 inch
B: 2.04 inch
C: 2.24 inch
D: 0.71 inch
E: 3/4 inch
F: 0.54 inch
G: 0.39 inch
H: 2.05 inch
I: 0.3 inch

Accessories

Optional accessories:



Limit Hands (green) 2pcs
Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application



Spindle Lifting Lever
for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4
Art No. 21EZA198
Price on application

Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application



Standard accessories:

Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*



Spare parts

Consumable spares:

Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*



