

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 2910AB-72

Images



Description

One Revolution Type for Error-free Reading

- Light weight type / standard type
- Limiting pointer rotation to one revolution eliminates the reading errors that can occur with dial indicators featuring more than one revolution of the pointer for full stroke.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0,008 "
Plunger Stroke:	2.2 mm
Range per rev.:	0.01 "
Dial reading:	4-0-4
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0.0001"
H MPE (Hysteresis):	0,0001"
R MPE (Repeatability):	±0,00003"
MPE first one revolution:	±0,0001"
Type:	ANSI/AGD Standard
Measuring force:	0,4-2,5 N
Stem:	9.52 mm / 0.375"

Contact point: Carbide tipped, thread: 4-48UNF


One revolution: Yes

Cushioned end point: Yes

Shockproof: Yes

Mass: 138 g

Dimensions



A: 1.86 inch

B: 2.02 inch

C: 2.24 inch

D: 0.71 inch

E: 3/4 inch

F: 0.54 inch

G: 0.36 inch

H: 2.05 inch

I: 0.3 inch

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application

Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application



Standard accessories:

Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*
Photo Not Available



Spare parts

Consumable spares:

Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*
Photo Not Available



