


Dial Gauge, Lug Back, ISO Type

Item number: 2929A-60

Images



Description

Graduation 0.01 / 0.1 mm

This is a one revolution dial indicator. It offers you the following benefits:


- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed without tools.
- No through screw holes on the frame and secure adhesion between the bezel and the crystal as well as the use of an O-ring prevents water or oil penetration.

Features

| | |
|------------------------|--------------------------------|
| Digital/Analog: | Analog |
| Inch-Metric: | Metric |
| Type: | EN ISO Standard |
| Delivered: | With certificate of inspection |
| Range: | 0.8 mm |
| Plunger Stroke: | 5 mm |
| Range per rev.: | 1 mm |
| Dial reading: | 40-0-40 |
| Graduation: | 0.01 mm |

| | |
|---------------------------------|---|
| MPE any 1/10 revolution: | 5 μm |
| MPE measuring range: | 7 μm |
| H MPE (Hysteresis): | 3 μm |
| R MPE (Repeatability): | 3 μm |
| Measuring force: | 0,4-2 N |
| Mass: | 146 g |
| Stem: | 8 mm |
| Contact point: | Carbide tipped, thread: M 2.5 x 0.45 mm |
| One revolution: | Yes |
| Shockproof: | Yes |

Dimensions



A: 47.2 mm

B: 70 mm

C: 57 mm

D: 18.1 mm

E: 20 mm

F: 12.3 mm

G: 29.2 mm

H: 52 mm

I: 7.6 mm

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application

Spare parts

Consumable spares:



Contact Element Ball Point, M2,5x0,45

7,3mm Length, Carbide, Metric

Art No. 901312

Suggested retail price: 14.00 €*



NBR Rubber Boot

Digital Gauge ID-B, Dial Gauge IP63/IP64

Art No. 21AAB562

Suggested retail price: 1.60 €*