

3-Point Internal Micrometer

Holtest Set

Item number: 368-918

Images



Description

- For setting 2-point bore gauges series 511.
- The Bore Gauge Checker allows easy setting of dial bore gauges with ranges of 18 mm through 400 mm using gauge blocks.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	0,8 - 2 "
Graduation:	≤ 0.5": 0.0001", >0.5": 0.0002"
Individual ranges:	0.8-1", 1-1.2", 1.2-1.6", 1.6-2"
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : ø 17 mm Over 12 mm : ø 23 mm
Measuring spindle:	Spindle pitch 0,635 mm
Measuring face:	Titanium coated tungsten carbide taper: tungsten carbide
Measuring method:	3-point
Models included:	368-266 / 368-267 / 368-268 / 368-269
Setting rings included:	ø1" (177-184) ø1.6" (177-291)
Delivered:	Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod
Mass:	960 g