


Dial Gauge, Flat Back, ISO Type

Item number: 2929AB-60

Images



Description

Graduation 0.01 / 0.1 mm

This is a one revolution dial indicator. It offers you the following benefits:


- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed without tools.
- No through screw holes on the frame and secure adhesion between the bezel and the crystal as well as the use of an O-ring prevents water or oil penetration.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Type:	EN ISO Standard
Range:	0.8 mm
Plunger Stroke:	5 mm
Range per rev.:	1 mm
Dial reading:	40-0-40
Delivered:	With certificate of inspection
Graduation:	0.01 mm

MPE any 1/10 revolution:	5 μm
MPE measuring range:	7 μm
H MPE (Hysteresis):	3 μm
R MPE (Repeatability):	3 μm
Measuring force:	0,4-2 N
Stem:	8 mm
Contact point:	Carbide tipped, thread: M 2.5 x 0.45 mm
One revolution:	Yes
Shockproof:	Yes
Mass:	137 g

Dimensions



A: 47.2 mm

B: 70 mm

C: 57 mm

D: 18.1 mm

E: 20 mm

F: 12.3 mm

G: 29.2 mm

H: 52 mm

I: 7.6 mm

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application

Spare parts

Consumable spares:



Contact Element Ball Point, M2,5x0,45

7,3mm Length, Carbide, Metric

Art No. 901312

Suggested retail price: 5.00 €*



NBR Rubber Boot

Digital Gauge ID-B, Dial Gauge IP63/IP64

Art No. 21AAB562

Suggested retail price: 7.00 €*