

## Digital ABS Caliper

Item number: 500-502-10

### Images



# ABSOLUTE<sup>®</sup>

### Description


This digimatic caliper allows you to take reliable measurements and offers you the following benefits:

- It has a robust design (6 x 25 mm beam) for large measuring ranges.
- ABSOLUTE System delivers reliable measurements.
- The slider provides smooth, stable and comfortable operation.
- Character height: 10 mm.

### Features

<b>Model:</b>	CD-100C
<b>Range:</b>	0 - 1,000 mm
<b>Delivered:</b>	Including SR44 battery
<b>Max. Permissible Error E MPE:</b>	$\pm 0,07$ mm
<b>Max. Permissible Error S MPE:</b>	$\pm 0,09$ mm
<b>Digital step:</b>	0,01 mm
<b>Max. response speed:</b>	Unlimited
<b>Display:</b>	LCD, character height 10 mm
<b>ORIGIN (ABS-Zero):</b>	Yes
<b>ON/OFF:</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b>Data output:</b>	Yes
<b>Battery life:</b>	Approx. 20000 hours
<b>Mass:</b>	3300 g

### Dimensions



**L:** 1240 mm

**A:** 50 mm

**B:** 60 mm

**C:** 49.8 mm

**D:** 130 mm

**H:** 32 mm

### Accessories

Optional accessories:



### **Digimatic Cable, Straight, Data Button,**

1m  
Art No. 959149  
Suggested retail price: 48.00 €\*  

---



### **Digimatic Cable, Straight, Data Button**

2m  
Art No. 959150  
Suggested retail price: 57.00 €\*  

---



### **USB Input Tool Direct (Digimatic to USB)**

2m Cable, Digimatic/Digimatic 2, Straight,  
with Data Button  
Art No. 06AFM380C  
Suggested retail price: 124.00 €\*  

---



### **U-WAVE-T, IP67 Type**

Wireless Transmitter  
Art No. 02AZD730G  
Suggested retail price: 187.00 €\*  

---



### **U-WAVE-T, Buzzer Type**

Wireless Transmitter  
Art No. 02AZD880G  
Suggested retail price: 187.00 €\*  

---



## Connection Cable C for U-WAVE

Straight, with Data Button  
Art No. 02AZD790C  
Suggested retail price: 105.00 €\*



## Data Hold Unit

for Digital Caliper  
Art No. 959143  
Suggested retail price: 39.50 €\*

### Spare parts

Consumable spares:



## Battery SR44 1,5 V

Art No. 938882  
Suggested retail price: 7.00 €\*