


2-Point Inside Measuring Instrument

Item number: 511-808

Images



Description

This is a micrometer head that enables measurements without interchangeable anvils. It offers you the following benefits:

- A long plunger stroke gives you amazing accuracy.
- Contact points are carbide (>18 mm range), giving you high durability and wear resistance.
- A large grip reduces heat transfer from the operator by 50%.
- Wide measuring range with sub-anvils.

Features

Digital/Analog:	Analog
Range:	600-800 mm
Accuracy:	2 μm
Repeatability:	0,5 μm
Delivered:	In a box with 2 sub-anvils, 2 spanner 200154

Dimensions

a: 16 mm
b: 250 mm
c: 120 mm
d: 185 mm
e: 300.9 mm
D1: 19.8 mm
D2: 15 mm
R1: SR10
R2: SR1.5

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Extension Rod Serie 511

125mm, 15mm Rod Diameter

Art No. 953557

Suggested retail price: 257.00 €*



Extension Rod Serie 511

250mm, 15mm Rod Diameter

Art No. 952361

Suggested retail price: 264.00 €*



Extension Rod Serie 511

500mm, 15mm Rod Diameter

Art No. 953558

Suggested retail price: 622.00 €*



Extension Rod Serie 511

750mm, 15mm Rod Diameter

Art No. 953559

Suggested retail price: 815.00 €*

Sub Anvil 100mm/511

Art No. 208932

Price on application



Spanner/102

Art No. 200154

Price on application

