


Dial Test Indicator, Universal Type

Item number: 513-302-10E

Images



Description


This is a Dial Test Indicator (Lever Type) which offers you the following benefits:

- Drastically enhanced durability, sensitivity and visibility.
- Glare-free flat crystal face allows easy reading of graduations.
- O-ring seal on the bezel has the effect of providing smooth rotation and prevents dust and oil from penetrating through to the dial face.
- The stylus length is on the dial face to reorder a replacement
- Multi-layer coatings on the crystal.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0,03 "
Dial reading:	0-15-0
Delivered:	In a box with stem $\varnothing 3/8"$ (9.52 mm), stylus $\varnothing 0.079"$, spanner
Graduation:	0.0005"
H MPE (Hysteresis):	0.0003"
R MPE (Repeatability):	$\pm 0.0003"$
MPE first one revolution:	$\pm 0.0005"$
Measuring force:	0,01-0,3 N
Contact point:	Thread M 1.4 x 0.3
Remarks:	Basic set
Mass:	71 g

Dimensions



L: 24 mm

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator

Art No. 21AAB363

Price on application

Standard accessories:



Art No. 21CAB105

Suggested retail price: 10.50 €*

Knurled Clamp Ring for Stem

Lever Indicator Serie 513

Art No. 190322

Suggested retail price: 5.80 €*



Stylus for Serie 513

D= 2mm, 6,5mm Length, Carbide
Art No. 102825
Suggested retail price: 14.50 €*



Spanner

Serie 513
Art No. 102037
Suggested retail price: 2.80 €*

