

Dial Gauge, Lug Back, ANSI/AGD Type

Item number: 3426A-19

Images



Description

This is a standard, inch dial indicator. It offers you the following benefits:


- Large-diameter dial face $\varnothing = 78$ mm for easy reading
- Supplied with limit markers and a bezel clamp as standard
- 0.001" / 0.0001" graduation

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	3 "
Range per rev.:	0,1"
Dial reading:	$\pm 0-100$
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0.001"
H MPE (Hysteresis):	0,00033"
R MPE (Repeatability):	$\pm 0,0002$ "
MPE first one revolution:	$\pm 0,001$ "
MPE first 2 1/2 revolutions:	$\pm 0,001$ "
MPE > 2 1/2-10 revolutions:	$\pm 0,002$ "
MPE > 10-20 revolutions:	$\pm 0,003$ "
MPE > 20 revolutions:	$\pm 0,005$ "

Type:	ANSI/AGD Standard
Measuring force:	0,4-3 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Continuous dial:	Yes
Coaxial revolution counter:	Yes
Shockproof:	Yes
Mass:	340 g

Dimensions



- A:** 4.84 inch
- B:** 7.8 inch
- C:** 3.07 inch
- D:** 0.7 inch
- E:** 3/4 inch
- F:** 2.91 inch
- G:** 3.35 inch
- H:** 2.8 inch
- I:** 0.35 inch

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB056

Suggested retail price: 8.30 €*
