


Dial Test Indicator, Horizontal Type

Item number: 513-404-10T

Images



Description


This is a dial test indicator (lever type) set which offers you the following benefits:

- Drastically enhanced durability, sensitivity and visibility
- Glare-free flat crystal face allows easy reading of graduations.
- O-ring seal on the bezel has the effect of providing smooth rotation and prevents dust and oil from penetrating through to the dial face.
- Multi-layer coatings on the crystal

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	0.8 mm
Dial reading:	0-40-0
Delivered:	In a box with stem $\varnothing 8/4$ mm, stylus $\varnothing 1/2/3$ mm, swivel clamp / holding bar
Graduation:	0.01 mm
MPE any 10 scale divisions:	5 μm
MPE any 1/2 revolution:	6 μm
MPE measuring range:	8 μm
H MPE (Hysteresis):	3 μm
R MPE (Repeatability):	3 μm
Measuring force:	0.01-0.3 N
Carbide stylus tip $\varnothing 2$ mm No.:	103006
Contact point:	Thread M 1.7 x 0.35
Remarks:	Full set
Mass:	45 g

Dimensions



Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.
Dial Indicator Series 1, Test Indicator
Art No. 21AAB363
Price on application

Standard accessories:



Stem for Standard Type Series 513

D=4mm

Art No. 21CAB106

Suggested retail price: 9.80 €*

Stem for Standard Type Series 513



D=8mm

Art No. 21CAB104

Suggested retail price: 6.50 €*

Stylus for Serie 513



D= 1mm, 17,4mm Length, Carbide

Art No. 103013

Suggested retail price: 7.30 €*

Stylus for Serie 513



D= 2mm, 17,4mm Length, Carbide

Art No. 103006

Suggested retail price: 14.50 €*

Stylus for Serie 513



D= 3mm, 17,4mm Length, Carbide

Art No. 103014

Suggested retail price: 7.30 €*

Knurled Clamp Ring for Stem

Lever Indicator Serie 513

Art No. 190322

Suggested retail price: **5.80 €***




Swivel Clamp

for D= 4/8mm, Dovetail

Art No. 900321

Suggested retail price: **26.50 €***



Holding Bar for Swivel Clamp

9x9mm, 100mm Length

Art No. 900209

Suggested retail price: **17.30 €***

