

2-Point Internal Micrometer

Holtest

Item number: 368-003

Images




Description

A non-digital 2-point Mitutoyo bore micrometer suitable for measuring the diameter of small holes. Hardened steel contact faces. Ratchet stop guarantees repeatable measurement. Steel setting rings (optional) are available for accurate setting prior to measurement.

Features

Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	3 - 4 mm
Graduation:	0,001 mm
Max. Permissible Error J MPE:	$\pm 2 \mu\text{m}$
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : $\varnothing 17 \text{ mm}$ Over 12 mm : $\varnothing 23 \text{ mm}$
Measuring spindle:	Spindle pitch 0,5 mm
Measuring face:	Tungsten carbide
Measuring method:	2-point
Delivered:	Including box, hex wrench, certificate of inspection, without setting ring
Mass:	91 g


Dimensions



c: 2 mm

L1: 22 mm

L2: 113 - 114 mm



c: 2 mm

L1: 22 mm

L2: 113 - 114 mm

Accessories

Optional accessories:



Setting Ring 3,0mm

Steel

Art No. 177-248

Suggested retail price: 126.00 €*



Setting Ring 4mm

Steel

Art No. 177-204

Suggested retail price: 126.00 €*