

3-Point Internal Micrometer

Holtest

Item number: 368-768

Images



Description


A non-digital Mitutoyo bore gauge. Hardened steel contact faces. A ratchet stop guarantees repeatable measurement.

Features

Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	30 - 40 mm
Graduation:	0,005 mm
Max. Permissible Error J MPE:	$\pm 3 \mu\text{m}$
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : $\varnothing 17 \text{ mm}$ Over 12 mm : $\varnothing 23 \text{ mm}$

Measuring spindle:	Spindle pitch 0,5 mm
Measuring face:	hardened steel Taper: hardened steel
Measuring method:	3-point
Delivered:	Including box, spanner, hex wrench, certificate of inspection, without setting ring
Mass:	290 g

Dimensions




a: 3.4 mm

b: 10 mm

L1: 145 - 155 mm

L2: 102 mm



a: 3.4 mm

b: 10 mm

L1: 145 - 155 mm

L2: 102 mm

Accessories

Optional accessories:



Holtest, Borematic Extension 150mm

for 20-50mm Measuring Range

Art No. 952622

Suggested retail price: 136.00 €*



Setting Ring 30mm

Steel

Art No. 177-288

Suggested retail price: 174.00 €*



Setting Ring 30mm

Ceramic
Art No. 177-431
Suggested retail price: 403.00 €*



Setting Ring 40mm

Steel
Art No. 177-290
Suggested retail price: 203.00 €*



Setting Ring 40mm

Ceramic
Art No. 177-433
Suggested retail price: 440.00 €*
