

3-Point Internal Micrometer

Holtest Set

Item number: 368-920

Images



Description

- For setting 2-point bore gauges series 511.
- The Bore Gauge Checker allows easy setting of dial bore gauges with ranges of 18 mm through 400 mm using gauge blocks.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	4 - 8 "
Graduation:	≤ 0.5": 0.0001", >0.5": 0.0002"
Individual ranges:	4-5", 5-6", 6-7", 7-8"
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : ø 17 mm Over 12 mm : ø 23 mm
Measuring spindle:	Spindle pitch 0,635 mm
Measuring face:	Titanium coated tungsten carbide taper: tungsten carbide

Measuring method: 3-point

Models included: 368-274 / 368-275 / 368-276 / 368-277

Setting rings included: \varnothing 5" (177-299)
 \varnothing 7" (177-303)

Delivered: Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod

Mass: 4680 g
