


Dial Test Indicator, Pocket Type

Item number: 513-512-10T

Images





Description


This is a small type Dial Test Indicator (Lever Type) which offers you the following benefits:

- Reversible measuring direction (clutch type)
- Jeweled bearings assure higher sensitivity and accuracy.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Delivered:	In a box with stem $\varnothing 3/8"$ (9,52 mm) / 0,157" (4 mm), stylus $\varnothing 0,039"/0,079"/0,118"$, swivel clamp / holding bar (2 pcs.)
Range:	0,02 "
Dial reading:	0-10-0
Graduation:	0.0005"
H MPE (Hysteresis):	0,0002"
R MPE (Repeatability):	$\pm 0,0002"$
MPE first one revolution:	$\pm 0.0005"$
Measuring force:	0,01-0,3 N
Carbide stylus tip $\varnothing 2$ mm No.:	131324
Mass:	51 g
Contact point:	Thread M 1.7 x 0.35
Remarks:	Full set

Dimensions



L1: 37.4 mm

L2: 33.9 mm mm

C: 74.1 mm

D Ø: 29.2 mm

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator

Art No. 21AAB363

Price on application

Standard accessories:



Stem for Pocket Type Serie 513

D=4mm

Art No. 102036

Suggested retail price: 11.00 €*

Stem

Ø 9,5mm

Art No. 102081

Price on application



Stylus for Series 513

D= 2mm, 33,9mm Length, Carbide
Art No. 131324
Suggested retail price: 12.00 €*



Stylus for Series 513

D= 1mm, 33,9mm Length, Carbide
Art No. 131316
Suggested retail price: 12.00 €*



Stylus for Series 513

D= 3mm, 33,9mm Length, Carbide
Art No. 131317
Suggested retail price: 12.00 €*



Swivel Clamp

for D= 4/9,52mm, Dovetail
Art No. 900322
Suggested retail price: 36.00 €*

Holding Bar for Swivel Clamp

12,7x6,35mm, 4" Length
Art No. 900306
Suggested retail price: 25.00 €*



Holding Bar for Swivel Clamp

D= 8mm, 115mm Length
Art No. 900211
Suggested retail price: 25.00 €*



Spanner R=7,3/4,5mm

Micrometer
Art No. 301336
Suggested retail price: 7.00 €*

