

Snap Meter for Mass-Produced Parts

Item number: 523-141

Images



Description

This Snap Gauge designed to mount an indicator to suit the measurement application, and offers the following benefits:

- It's ideal for rapidly inspecting workpieces, especially cylindrical, in batch or mass production situations, when you need an indication of where a measurement falls within the tolerance band.
- You can set it with external length standards such as block gauges.
- Easy-to-operate retracting button.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	0 - 25 mm
Delivered:	Including box, workpiece rest, without indicator
Anvil retracting stroke:	2 mm
Repeatability:	0.4 μ m
Flatness:	0,3 μ m
Parallelism:	0,6 μ m
Measuring face:	Carbide-tipped, micro-lap finish \varnothing 10.8 mm

Measuring spindle: ø10,8 mm

Measuring force: 5 - 10 N

Mass: 710 g

Dimensions

Accessories

Optional accessories:

Promotion!



Dial Gauge, Flat Back, ISO Type

Jewelled Bearing, Shockproof, 1mm, 0,001mm

Art No. 2109AB-10

Promo price: **84.00 €***

Suggested retail price: ~~106.00 €*~~



Dial Gauge, Flat Back, ISO Type

One Revolution, Jewelled Bearing, Shockproof, 0,08mm, 0,001mm

Art No. 2900AB-10

Suggested retail price: **158.00 €***

Promotion!



Digital Indicator ID-C

12,7mm, 0,0005mm, Flat Back Plate

Art No. 543-700B

Promo price: **349.00 €***

Suggested retail price: ~~446.00 €*~~