


Dial Test Indicator, Horiz. 20° Face

Item number: 513-445-10E

Images



Description

This is a Dial Test Indicator (Lever Type) which offers you the following benefits:


- Drastically enhanced durability, sensitivity and visibility.
- Glare-free flat crystal face allows easy reading of graduations.
- O-ring seal on the bezel has the effect of providing smooth rotation and prevents dust and oil from penetrating through to the dial face.
- The stylus length is on the dial face to reorder a replacement
- Multi-layer coatings on the crystal.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Delivered:	In a box with stem ø8 mm, stylus ø2 mm
Range:	0.4 mm
Dial reading:	0-100-0
Graduation:	0.002 mm

MPE any 10 scale divisions:	2 μm
MPE any 1/2 revolution:	3 μm
MPE any 1 revolution:	5 μm
MPE measuring range:	6 μm
H MPE (Hysteresis):	4 μm
R MPE (Repeatability):	1 μm
Measuring force:	0,01-0,3 N
Carbide stylus tip $\varnothing 2$ mm No.:	103011
Mass:	48 g
Contact point:	Thread M 1.7 x 0.35
Remarks:	Basic set

Dimensions



Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator
Art No. 21AAB363
Price on application

Standard accessories:



Stem for Standard Type Series 513

D=8mm
Art No. 21CAB104
Suggested retail price: 15.00 €*



Knurled Clamp Ring for Stem

Lever Indicator Serie 513
Art No. 190322
Suggested retail price: 12.00 €*



Stylus for Serie 513

D= 2mm, 15,2mm Length, Carbide
Art No. 103011
Suggested retail price: 21.00 €*
