

Steel Individual Inch Gauge Block 0.127"

Item number: 614167

Images



Mitutoyo

Certificate number: TMS02000
page 1 of 1

CERTIFICATE OF INSPECTION

Instrument: Gauge Block
Grade: G (G10)

Date of inspection: 18th May, 2006 Unit: in, inch

Block	Ident. No.	Central Deviation	Maximum Deviation	Minimum Deviation	Variation
1	06280	-0.4	+1.2	-0.4	1.6

ENVIRONMENT: Air temperature: $68 \pm 1.0^\circ\text{F}$ ($20 \pm 1.0^\circ\text{C}$)
 BASE OF TEST: NIST 98B.1.9-2002
 MATERIAL: Steel
 INSPECTION METHOD: by comparison
 COEFFICIENT OF THERMAL EXPANSION: $61.8 \times 10^{-6} \text{ in/in/}^\circ\text{F}$ ($110.8 \times 10^{-6} \text{ in/in/}^\circ\text{C}$)
 EXTENDED UNCERTAINTY: $\pm 0.0001 \text{ in}$ for Size 0.127 in (Reference length: 1 inch)
 PER Gauge Dimension: $\pm 0.0001 \text{ in}$ (0.127 in, 1.27 in)
 QUALITY SYSTEM: ISO 9001 Registered Firm - ISO 9000
 TRACEABILITY: Reported in NIST No. 607-2000-02
 (2007 Edition, Institute of Standards and Technology)

Date: 18th May, 2006

S. S. S. S.
S. S. S. S.

F-0110
Mitutoyo Co., Ltd.
1-1-1, Higashi-cho, Takamachi-ku, Osaka
590-8501, Japan

