

## Steel Individual Inch Gauge Block 0.7"

Item number: 614197

### Images



Mitutoyo Certificate number: TMS020000 page 1 of 1

### CERTIFICATE OF INSPECTION

Instrument: Gauge Block  
Grade: G (G6)

Date of inspection: 18th May, 2006 Unit: in, inch

Block	Ident. No.	Central Deviation	Maximum Deviation	Minimum Deviation	Variation
1	06200	-0.4	+1.2	-0.4	1.6

ENVIRONMENT: Air temperature: 68 ± 1.0°F (20 ± 1.0°C)  
 BASE OF REST: 6061-T6 ALUMINUM  
 MATERIAL: Steel  
 INSPECTION METHOD: by comparison  
 COEFFICIENT OF THERMAL EXPANSION: 61.8 x 10<sup>-6</sup> / °F (111.8 x 10<sup>-6</sup> / °C) (10.8 x 10<sup>-6</sup> / °F) (19.4 x 10<sup>-6</sup> / °C)  
 EXTENDED UNCERTAINTY: ± 0.0001 in (0.0025 mm) (0.001 in) (0.025 mm) (0.001 in) (0.025 mm) (0.001 in) (0.025 mm)  
 PER GAUGE DIMENSION: 0.0001 in (0.0025 mm) (0.001 in) (0.025 mm) (0.001 in) (0.025 mm)  
 QUALITY SYSTEM: ISO 9001 Registered Firm - 60-300000  
 TRACEABILITY: Traceable to NIST 601/2000A-02 (2000/2000A-02) (International of Standards and Technical)

Date: 18th May, 2006

*S. S. S. S.*

F-01101

