

Steel Individual Inch Gauge Block 0.0625"

Item number: 614303

Images



Mitutoyo Certificate number: TMS020000 page 1 of 1

CERTIFICATE OF INSPECTION

Instrument: Gauge Block
 Grade: G (G10)

Date of inspection: 18th May, 2006 Unit: in, inch

Block	Ident. No.	Central Deviation	Maximum Deviation	Minimum Deviation	Variation
1	06250	-0.4	+1.2	-0.4	1.6

ENVIRONMENT: Air temperature: 68 ± 1.0°F (20 ± 1.0°C)
 BASE OF REST: 6061 ALUMINUM
 MATERIAL: Steel
 INSPECTION METHOD: by comparison
 COEFFICIENT OF THERMAL EXPANSION: 61.8 x 10⁻⁶ in/in/°F (110.8 x 10⁻⁶ m/m/°C)
 EXTENDED UNCERTAINTY: ± 0.0001 in (± 0.0025 mm) (k=2)
 PER GAUGE SURFACES: 100% (0.2 x 1 / 1.0) at each face
 QUALITY SYSTEM: ISO 9001 Registered Firm - GB, MICHIGAN
 TRACEABILITY: Traceable to NIST 601/2000A-02 (2000/2001a) Institute of Standards and Technology

Date: 18th May, 2006

S. S. S. S.

