


## Dial Test Indicator, Pocket Type

Item number: 513-515-10T

**Images**





**Description**


This is a small type Dial Test Indicator (Lever Type) which offers you the following benefits:

- Reversible measuring direction (clutch type)
- Jeweled bearings assure higher sensitivity and accuracy.

**Features**

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	1 mm
<b>Dial reading:</b>	0-50-0
<b>Delivered:</b>	In a box with stem $\varnothing 4/8$ mm, stylus $\varnothing 2$ mm, swivel clamp / holding bar (2 pcs.)
<b>Graduation:</b>	0.01 mm
<b>H MPE (Hysteresis):</b>	4 $\mu$ m
<b>MPE any 10 scale divisions:</b>	5 $\mu$ m
<b>MPE any 1/2 revolution:</b>	8 $\mu$ m
<b>MPE measuring range:</b>	10 $\mu$ m
<b>R MPE (Repeatability):</b>	3 $\mu$ m
<b>Measuring force:</b>	$\leq 0,3$ N
<b>Carbide stylus tip <math>\varnothing 2</math> mm No.:</b>	136013
<b>Contact point:</b>	Thread M 1.7 x 0.35
<b>Remarks:</b>	Full set

**Dimensions**



**L1:** 44.5 mm

**L2:** 41 mm

**C:** 81.2 mm

## Accessories

### Optional accessories:



### Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator

Art No. 21AAB363

Price on application

### Standard accessories:



### Gambo per Serie 513

D=4mm

Art No. 102036

Suggested retail price: 5.80 €\*



### Stem for Serie 513

D= 8mm

Art No. 102822

Suggested retail price: 5.80 €\*

### Stylus for Serie 513

D= 2mm, 41mm Length, Carbide  
Art No. 136013  
Suggested retail price: 9.50 €\*  


---



### Swivel Clamp

for D= 4/8mm, Dovetail  
Art No. 900321  
Suggested retail price: 26.50 €\*  

---



### Holding Bar for Swivel Clamp

9x9mm, 100mm Length  
Art No. 900209  
Suggested retail price: 17.30 €\*  

---



### Holding Bar for Swivel Clamp

D= 8mm, 115mm Length  
Art No. 900211  
Suggested retail price: 17.30 €\*  

---



### Spanner R=7,3/4,5mm

Micrometer  
Art No. 301336  
Suggested retail price: 4.20 €\*  

---

