

800HK0,05 Knoop Hardness

Reference Material

Item number: 63ETB1220

Images



Description

Hardness reference materials in quality control:

The boost for your process safety! The daily verification, performed by the user, is described in the according hardness testing standards and significantly contributes to quality management processes.

In the daily verification process, all parameters of the hardness test system that build up to the hardness value, are examined by indentations on the hardness reference material.

This periodical inspection of the machine by means of hardness reference materials should be carried out immediately before the daily start of the test schedule. An according documentation enhances the process safety, as value shifts due to damage or malfunction can be detected easily. In addition, the repeatability of results of the hardness testing machine can also be checked with the hardness reference materials.

Mitutoyo offers a comprehensive range of hardness reference materials (hardness test blocks) in different materials with hardness levels ranging from **200** to **2100HK** to suit your quality management procedure perfectly.

The tolerance for the nominal value of steel and aluminium hardness testblocks is **± 25HK**. (Does not apply for carbide materials) For carbide reference materials, the actual calibrated value can be significantly higher.

Mitutoyo reference materials:

High-end quality Made in Germany - Independent DAkkS calibration according to **DIN EN ISO 4545** and/or **ASTM E92** in an accredited laboratory Large square or rectangular surface with large space advantage over triangular or round test blocks Short delivery time MPE "Maximum Permissible Error" of the hardness testing system engraved (does apply for carbide materials) – all relevant information at a glance.

If the diagonal lengths are outside the **20µm** limit of **ISO 4545** the reference material is exclusively supplied with **ASTM E92** calibration certificates.

A range of additional services can be ordered:

- Up to three different scales on one reference material (Does not apply for Brinell materials)
- A lasered grid on the surface for accurate indentation spacing
- Alternative ASTM accredited calibration.
- Double calibration according to **ISO** and **ASTM** standards
- A tighter tolerance of **± 15HK** for the nominal value (Does not apply for carbide materials)
- Compare the surface sizes for the evaluation of the price - performance ratio.

Please contact us if you do not find what you are looking for.

Features

Description:	Optional availability: ■ calibration of up 3 test scales on one test block ■ calibration according to ASTM E92 ■ lasered grid for accurate indentation spacing
Method:	Knoop
Material:	steel
Hardness Value:	800
Scale 1:	HK0,05
Indenter:	Diamond pyramid
Standard:	ISO 4545-3
Test Force N:	0.4903
Test Force kgf:	0.05
Accreditation body:	DAkkS
Accreditation standard:	ISO 17025
Dimension:	30x30x6mm
Surface:	900mm2
Net weight:	50 g
Gross weight:	160 g
Product line:	■ HM-210 ■ HM-220