


2-Point Inside Measuring Instrument

Item number: 526-101

Images



Description


This is a two point split contact point ideally suited to smaller bore measurements. It offers you the following benefits:

- A precision bore gauge so you can make quick and accurate measurements of small hole diameters (0.95-18 mm).
- You can replace the analogue indicator fitted to this instrument with a customer-supplied Digimatic indicator if you need.
- The contact point is hard chrome coated.

Features

Inch-Metric:	Metric
Range:	0.95 - 1.55 "
Range:	7 - 10 mm
Graduation:	0.001 mm
Accuracy:	4 μ m
Repeatability:	2 μ m
Number of anvils:	6
Delivered:	In a box, without dial indicator, cover for dial indicator and setting ring

Dimensions



Accessories

Optional accessories:



Stand for Bore Gauge Series 526

D=60mm Table, 38mm Table Stroke
Art No. 215-120-10
Suggested retail price: 1,178.00 €*



Digital Indicator, Bore Gauge ID-C

12,7mm, 0,001mm, Flat Back Plate
Art No. 543-310B-10
Suggested retail price: 563.00 €*



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application

Standard accessories:



Contact Point for Serie 526

7-7,5mm
Art No. 102469
Suggested retail price: 66.00 €*



Contact Point for Serie 526

7,7-8mm
Art No. 102470
Suggested retail price: 66.00 €*



Contact Point for Serie 526

8-8,5mm
Art No. 102471
Suggested retail price: 66.00 €*



Contact Point for Serie 526

8,5-9mm
Art No. 102472
Suggested retail price: 66.00 €*



Contact Point for Serie 526

9-9,5mm
Art No. 102473
Suggested retail price: 66.00 €*



Contact Point for Serie 526

9,5-10mm
Art No. 102474
Suggested retail price: 66.00 €*



Spanner/526

Art No. 102148

Price on application