


## 2-Point Inside Measuring Instrument

Item number: 526-103

### Images



### Description


This is a two point split contact point ideally suited to smaller bore measurements. It offers you the following benefits:

- A precision bore gauge so you can make quick and accurate measurements of small hole diameters (0.95-18 mm).
- You can replace the analogue indicator fitted to this instrument with a customer-supplied Digimatic indicator if you need.
- The contact point is hard chrome coated.

### Features

<b>Range:</b>	0,3 - 0,4 "
<b>Repeatability:</b>	2 $\mu$ m
<b>Number of anvils:</b>	6
<b>Delivered:</b>	In a box, without dial indicator, cover for dial indicator and setting ring

### Dimensions



### Accessories

Optional accessories:



## Stand for Bore Gauge Series 526

D=60mm Table, 38mm Table Stroke  
Art No. 215-120-10  
Suggested retail price: 1,178.00 €\*



## Digital Indicator, Bore Gauge ID-C

ASME/ANSI Type, Inch/Metric, 0,5", 0,00005",  
Flat Back Plate  
Art No. 543-312B-10  
Suggested retail price: 563.00 €\*



## Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4  
Art No. 21AZB195  
Price on application

Standard accessories:



## Contact Point for Serie 526

7-7,5mm  
Art No. 102469  
Suggested retail price: 66.00 €\*



### Contact Point for Serie 526

7,7-8mm  
Art No. 102470  
Suggested retail price: 66.00 €\*  

---



### Contact Point for Serie 526

8-8,5mm  
Art No. 102471  
Suggested retail price: 66.00 €\*  

---



### Contact Point for Serie 526

8,5-9mm  
Art No. 102472  
Suggested retail price: 66.00 €\*  

---



### Contact Point for Serie 526

9-9,5mm  
Art No. 102473  
Suggested retail price: 66.00 €\*  

---



### Contact Point for Serie 526

9,5-10mm  
Art No. 102474  
Suggested retail price: 66.00 €\*  

---



## Spanner/526

Art No. 102148

Price on application