

Steel Individual Inch Gauge Block 0.118"

Item number: 614158

Images



Mitutoyo Certificate number: TMS020000 page 1 of 1

CERTIFICATE OF INSPECTION

Instrument: Gauge Block
Grade: G (G18)

Date of inspection: 18th May, 2006 Unit: in, inch

Block	Ident. No.	Central Deviation	Maximum Deviation	Minimum Deviation	Variation
1	06280	-0.4	+1.2	-0.4	1.6

ENVIRONMENT: Air temperature: 68 ± 1.0°F (20 ± 1.0°C)
 BASE OF REST: 6061-T6 ALUMINUM
 MATERIAL: Steel
 INSPECTION METHOD: by comparison
 COEFFICIENT OF THERMAL EXPANSION: 61.8 x 10⁻⁶ / °F (111.8 x 10⁻⁶ / °C) (10.8 x 10⁻⁶ / °F) (19.4 x 10⁻⁶ / °C)
 EXTENDED UNCERTAINTY: ± 0.0001 in (0.0025 mm) (0.001 in) (0.025 mm) (0.001 in) (0.025 mm) (0.001 in) (0.025 mm)
 PER GAUGE DIMENSION: 0.118 in (3.0 mm) (0.118 in) (3.0 mm) (0.118 in) (3.0 mm) (0.118 in) (3.0 mm)
 QUALITY SYSTEM: ISO 9001 Registered Firm - 60-300000
 TRACEABILITY: Traceable to NIST 601-2000A-01 (2000) (National Institute of Standards and Technology)

Date: 18th May, 2006

S. S. S. S.
S. S. S. S.

