

Steel Individual Inch Gauge Block 0.125"

Item number: 614165

Images



Mitutoyo Certificate number: TMS020000 page 1 of 1

CERTIFICATE OF INSPECTION

Instrument: Gauge Block
Grade: G (GMS)

Date of inspection: 18th May, 2006 Unit: in, inch

Block	Ident. No.	Central Deviation	Maximum Deviation	Minimum Deviation	Variation
1	06280	-0.4	+1.2	-0.4	1.6

ENVIRONMENT: Air temperature: $68 \pm 1.0^\circ\text{F}$ ($20 \pm 1.0^\circ\text{C}$)
 BASE OF TEST: 606 988.1, 9-2002
 MATERIAL: Steel
 INSPECTION METHOD: by comparison
 COEFFICIENT OF THERMAL EXPANSION: $61.8 \times 10^{-6} / ^\circ\text{F}$ ($110.8 \times 10^{-6} / ^\circ\text{C}$)
 EXTENDED UNCERTAINTY: ± 0.0001 in, ± 0.0025 mm (k=2)
 PER GAUGE DIMENSION: ± 0.0001 in, ± 0.0025 mm (k=2)
 QUALITY SYSTEM: ISO 9001 Registered Firm - GB, MITSUBISHI
 TRACEABILITY: Traceable to NIST 481/2000A-02 (2000/2001a) International of Standards and Technicality

Date: 18th May, 2006

S. S. S. S.
S. S. S. S.

F-01101
 0.125 in
 0.125 in
 0.125 in

