

Steel Individual Inch Gauge Block 0.131"

Item number: 614171

Images



Mitutoyo Certificate number: TMS020000 page 1 of 1

CERTIFICATE OF INSPECTION

Instrument: Gauge Block
Grade: G (G10)

Date of inspection: 18th May, 2006 Unit: in, inch

Block	Ident. No.	Central Deviation	Maximum Deviation	Minimum Deviation	Variation
1	06280	-0.4	+1.2	-0.4	1.6

ENVIRONMENT: Air temperature: 68 ± 1.0°F (20 ± 1.0°C)
 BASE OF REST: 6061 ALUMINUM
 MATERIAL: Steel
 INSPECTION METHOD: by comparison
 COEFFICIENT OF THERMAL EXPANSION: 61.8 x 10⁻⁶ / °F (110.8 x 10⁻⁶ / °C) (10.8 x 10⁻⁶ / °F) (19.4 x 10⁻⁶ / °C)
 EXTENDED UNCERTAINTY: ± 0.0001 inch (± 0.0025 mm) (± 0.0001 inch) (± 0.0025 mm)
 PER GAUGE DIMENSION: 0.131 inch (± 0.0001 inch) (± 0.0025 mm) (± 0.0001 inch) (± 0.0025 mm)
 QUALITY SYSTEM: ISO 9001 Registered Firm - GB, MICHIGAN
 TRACEABILITY: Reported in NIST No. 800-20000-02 (2000) (National Institute of Standards and Technology)

Date: 18th May, 2006
 S. S. S. S.

F-411 (G) 0.131 inch (0.131 inch) (0.131 inch) (0.131 inch) (0.131 inch) (0.131 inch)

