

450HV1 Vickers Hardness Reference Material

Item number: 63ETB769

Images



Description

Hardness reference materials in quality control:

The boost for your process safety! The daily verification, performed by the user, is described in the according hardness testing standards and significantly contributes to quality management processes. In the daily verification process, all parameters of the hardness test system that build up to the hardness value, are examined by indentations on the hardness reference material.

This periodical inspection of the machine by means of hardness reference materials should be carried out immediately before the daily start of the test schedule.

An according documentation enhances the process safety, as value shifts due to damage or malfunction can be detected easily. In addition, the repeatability of results of the hardness testing machine can also be checked with the hardness reference materials.

Mitutoyo offers a comprehensive range of **hardness reference materials** (hardness test blocks) in different materials with hardness levels ranging from **80HV** to **2100HV** to suit your quality management procedure perfectly.

The tolerance for the nominal value of steel and aluminium hardness testblocks is $\pm 25HV$. (Does not apply for carbide materials) For carbide reference materials, the actual calibrated value can be significantly higher.

Mitutoyo reference materials:

High-end quality **Made in Germany** - Independent **DAkkS** calibration according to **DIN EN ISO 6507** and/or **ASTM E92** in an accredited laboratory Large square or rectangular surface with large space advantage over triangular or round test blocks Short delivery time MPE "Maximum Permissible Error" of the hardness testing system engraved (does apply for carbide materials) - all relevant information at a glance.

If the diagonal lengths are outside the **20µm** limit of ISO 6507 the reference material is exclusively supplied with ASTM E92 calibration certificates.

A range of additional services can be ordered:

- Up to three different scales on one reference material (Does not apply for Brinell materials)
- A lasered grid on the surface for accurate indentation spacing
- Alternative **ASTM** accredited calibration.
- Double calibration according to **ISO** and **ASTM** standards
- A tighter tolerance of $\pm 15HV$ for the nominal value (Does not apply for carbide materials)

Compare the surface sizes for the evaluation of the price - performance ratio.

Please contact us if you do not find what you are looking for.

Features

Description: Optional availability:

- calibration of up 3 test scales on one test block
- calibration according to ASTM E92
- lasered grid for accurate indentation spacing

Functions: 3. Vickers Test Block with DAkKS / ISO certificate

Method: Vickers

Material: steel

Hardness Value: 450

Scale 1: HV1

Tolerance of nominal value: ±25HV

Indenter: Diamond pyramid

Standard: ISO 6507-3

Test Force N: 9.807

Test Force kgf: 1

Accreditation body: DAkKS

Accreditation standard: ISO 17025

Dimension: 60x60x16mm

Surface: 3.600 mm²

Net weight: 450 g

Gross weight: 560 g

Product line:

- HM-210
- HM-220
- HV-110
- HV-120