


## Dial Indicator Thickness Gauge

Item number: 7315A

### Images




### Description

This Dial Indicator Thickness Gauge enables you to measure tube wall thickness, film/paper etc. with flat contact points, resp. lens thickness or groove depth.

### Features

<b>Inch-Metric:</b>	Metric
<b>Functions:</b>	Knife-edge contact point
<b>Delivered:</b>	In a box with spindle lifting lever 21AZB149
<b>Range:</b>	0 - 10 mm
<b>Graduation:</b>	0.01 mm
<b>Parallelism:</b>	5 $\mu$ m
<b>Indicator No.:</b>	2,046AB
<b>Max. measuring depth:</b>	30 mm
<b>Measuring force:</b>	$\leq 1,4$ N
<b>Mass:</b>	220 g
<b>Contact point:</b>	Thread M 2.5 x 0.45 mm
<b>Type:</b>	Knife-edge contact point

### Dimensions



### Accessories

Optional accessories:



### Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



### Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

Price on application

### Spare parts

Consumable spares:



### Spindle Lifting Lever

for S-Type Serie 2,3,4 up to 10mm/0,4"

Art No. 21AZB149

Price on application



### Spindle Lifting Lever

for S and A-Type Serie 2,3 >10/0,4" up to 20mm/0,8"

Art No. 21AZB150

Price on application