


Dial Indicator Thickness Gauge

Item number: 7360A

Images




Description

This Dial Indicator Thickness Gauge enables you to measure tube wall thickness, film/paper etc. with flat contact points, resp. lens thickness or groove depth.

Features

Inch-Metric:	Metric
Functions:	Tube thicknesses - Minimum inside diameter 3,5 mm
Delivered:	In a box with spindle lifting lever 21AZB149
Range:	0 - 10 mm
Graduation:	0.01 mm
Indicator No.:	2,046AB
Max. measuring depth:	20 mm
Measuring force:	$\leq 1,4$ N
Mass:	200 g
Contact point:	Thread M 2.5 x 0.45 mm
Type:	Tube thicknesses - Minimum inside diameter 3,5 mm

Dimensions



Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Bezel Clamp for Dial Gauge

Metric, Series 2/3/4

Art No. 21AZB148

Price on application

Spare parts

Consumable spares:



Spindle Lifting Lever

for S-Type Serie 2,3,4 up to 10mm/0,4"

Art No. 21AZB149

Price on application



Spindle Lifting Lever

for S and A-Type Serie 2,3 >10/0,4" up to 20mm/0,8"

Art No. 21AZB150

Price on application