


## Stylus M2 ruby ball Ø4,0mm

Item number: K651017

### Images



### Description

Straight styli are used to detect easily reachable features on the measured surface. Ruby, as the hardest of all stylus tip materials, is the perfect choice for most applications. Stainless steel is the primary material of choice for high-strength precision styli and extensions. If weight can be disregarded, because of the adhesive material build up, the scanning of aluminium surfaces with ruby tips is not recommended.

### Features

<b>Description protocol system:</b>	01-M2-R4-L10-ML10-SS1,5-BS3
<b>Thread:</b>	M2
<b>Ball Material:</b>	ruby
<b>Ball ø:</b>	4 mm
<b>Ball Grade DIN 5401:</b>	Grade 5
<b>Base material:</b>	stainless steel
<b>Tool Bore Ø:</b>	1.3 mm
<b>Shaft stem material:</b>	stainless steel
<b>Effective length:</b>	10 mm
<b>Renishaw Code No.:</b>	A-5000-4154
<b>ITP Code No.:</b>	TI M2 040 03 012
<b>Qmark Code No.:</b>	TM2-4010-S
<b>Mass:</b>	0,42 g

### Dimensions

