


Stylus M3 ruby ball Ø3,0mm

Item number: K651143

Images



Description

Straight styli are used to detect easily reachable features on the measured surface. Ruby, as the hardest of all stylus tip materials, is the perfect choice for most applications. Bend-resistant styli stems made of tungsten carbide are ideal for virtually all standard applications in the measuring lab with its high rigidity properties. Because of the adhesive material build up, the scanning of aluminium surfaces with ruby tips is not recommended.

Features

Description protocol system:	01-M3-R3-L50-ML43-SCER2-BS4
Thread:	M3
Ball Material:	ruby
Ball ø:	3 mm
Ball Grade DIN 5401:	Grade 5
Base material:	stainless steel
Tool Bore Ø:	1.3 mm
Shaft stem material:	carbide
Effective length:	43 mm
Renishaw Code No.:	A-5003-0067
ITP Code No.:	TK M3 030 04 051
Qmark Code No.:	TM3-3051.5-C
Mass:	1,19 g

Dimensions

