


Stylus M3 ruby ball Ø3,0mm

Item number: K651148

Images



Description

Straight styli are used to detect easily reachable features on the measured surface. Ruby, as the hardest of all stylus tip materials, is the perfect choice for most applications. Stainless steel is the primary material of choice for high-strength precision styli and extensions. If weight can be disregarded. Because of the adhesive material build up, the scanning of aluminium surfaces with ruby tips is not recommended.

Features

Description protocol system:	01-M3-R3-L21-ML12-SS1,5-BS4
Thread:	M3
Ball Material:	ruby
Ball ø:	3 mm
Ball Grade DIN 5401:	Grade 5
Base material:	stainless steel
Tool Bore Ø:	1.3 mm
Shaft stem material:	stainless steel
Effective length:	12 mm
Renishaw Code No.:	A-5000-3553
ITP Code No.:	TI M3 030 04 022
Qmark Code No.:	TM3-3022-S
Romer CodeNo.:	NCA7-7-19997
Mass:	0,96 g

Dimensions

