


Stylus M3 ruby ball Ø4,0mm

Item number: K651149

Images



Description

Straight styli are used to detect easily reachable features on the measured surface. Ruby, as the hardest of all stylus tip materials, is the perfect choice for most applications. Stainless steel is the primary material of choice for high-strength precision styli and extensions. If weight can be disregarded, because of the adhesive material build up, the scanning of aluminium surfaces with ruby tips is not recommended.

Features

Description protocol system:	01-M3-R4-L21-ML17-SS2,5-BS4
Thread:	M3
Ball Material:	ruby
Ball ø:	4 mm
Ball Grade DIN 5401:	Grade 5
Base material:	stainless steel
Tool Bore Ø:	1.3 mm
Shaft stem material:	stainless steel
Effective length:	17 mm
Renishaw Code No.:	A-5000-7606
ITP Code No.:	TI M3 040 04 023
Qmark Code No.:	TM3-4023-S
Mass:	1,38 g

Dimensions

