


Stylus M2 ruby ball Ø5,0mm

Item number: K651328

Images



Description

Straight styli are used to detect easily reachable features on the measured surface. Ruby, as the hardest of all stylus tip materials, is the perfect choice for most applications. The very lightweight and extremely stiff character of ceramic materials and its low thermal expansion, makes it the ideal material, especially for long stems and extensions. The brittle characteristic can protect probes from the effects of crash. Because of the adhesive material build up, the scanning of aluminium surfaces with ruby tips is not recommended.

Features

Description protocol system:	01-M2-R5-97,5-ML97,5-SCER3-BS3
Thread:	M2
Ball Material:	ruby
Ball ø:	5 mm
Ball Grade DIN 5401:	Grade 5
Base material:	stainless steel
Tool Bore Ø:	1.3 mm
Shaft stem material:	ceramic
Effective length:	97.5 mm
Mass:	2,99 g

Dimensions

