


Stylus M2 ruby ball Ø4,0mm

Item number: K651744

Images



Description

Straight styli are used to detect easily reachable features on the measured surface. Ruby, as the hardest of all stylus tip materials, is the perfect choice for most applications. Bend-resistant styli stems made of tungsten carbide are ideal for virtually all standard applications in the measuring lab with its high rigidity properties. Stainless steel is the primary material of choice for high-strength precision styli and extensions if weight can be disregarded. Because of the adhesive material build up, the scanning of aluminium surfaces with ruby tips is not recommended.

Features

Description protocol system:	01-M2-R46-L12,15-ML12,15-SWC1,5-BS3
Thread:	M2
Ball Material:	ruby
Ball ø:	4 mm
Ball Grade DIN 5401:	Grade 5
Base material:	stainless steel
Tool Bore Ø:	2 mm
Shaft stem material:	carbide
Effective length:	12.15 mm
Renishaw Code No.:	A-5004-2182
Mass:	1.2 g

Dimensions

