


M8 male 90° snap-in with cable

PVC 4x0.25 gy UL/CSA 10m


Male 90°  
M8 (Snap In), 4-pole  
with cable sleeves  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Illustration



Product may differ from Image

Approvals



\* only for products with UL/CSA approved cable

Form

Form 08191

General data

|                           |                                          |
|---------------------------|------------------------------------------|
| Standards                 | DIN EN 61076-2-104 (M8)                  |
| Pollution Degree          | 3                                        |
| Stripping length (jacket) | 20 mm                                    |
| Temperature range         | -25...+85 °C, depending on cable quality |

Cables

|                      |     |
|----------------------|-----|
| Cable identification | 211 |
|----------------------|-----|

|                                    |                                                |
|------------------------------------|------------------------------------------------|
| Cable Type                         | 1 (PVC)                                        |
| Approval (cable)                   | UL (AWM-Style 2464/1731), CSA                  |
| Cable weight [g/m]                 | 34,76                                          |
| Material (wire)                    | Cu wire, bare                                  |
| Resistor (core)                    | max. 79 $\Omega$ /km (20 °C)                   |
| Single wire Ø (core)               | 0.15 mm                                        |
| Construction (core)                | 14× 0.15 mm (multi-strand wire class 5)        |
| Diameter (core)                    | 4× 0.25 mm <sup>2</sup>                        |
| AWG                                | similar to AWG 24                              |
| Material (wire isolation)          | PVC                                            |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (wire isolation)    | 45 ±5 D                                        |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                    |
| Color/numbering of wires           | br, bk, bl, wh                                 |
| Stranding combination              | 4 wires twisted                                |
| Shield                             | no                                             |
| Material (jacket)                  | PVC                                            |
| Material property (jacket)         | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (jacket)            | 85 ±5 A                                        |
| Outer-Ø (jacket)                   | 4.8 mm ±5%                                     |
| Color (jacket)                     | gray                                           |
| chemical resistance                | good resistance to oil, gasoline and chemicals |
| thermal resistance                 | flame retardant UL 1581 VW1 / CSA FT1          |
| Nominal voltage                    | UL 300 V AC                                    |
| Test voltage                       | 2000 V AC                                      |
| Current load capacity              | to DIN VDE 0298-4                              |
| Temperature range (fixed)          | -30...+80 °C                                   |
| Temperature range (mobile)         | -5...+80 °C                                    |
| Bend radius (fixed)                | 5× outer Ø                                     |
| Bend radius (moving)               | 10× outer Ø                                    |
| No./diameter of wires              | 4× 0.25 mm <sup>2</sup>                        |
| Wire isolation                     | PVC (br, wh, bl, bk)                           |
| Jacket Color                       | gray                                           |
| Material (jacket)                  | PVC (UL/CSA)                                   |
| Outer Ø                            | 4.8 mm ±5%                                     |
| Bend radius (moving)               | 10× outer Ø                                    |
| Temperature range (fixed)          | -30...+80 °C                                   |
| Temperature range (mobile)         | -5...+80 °C                                    |

#### Technical Data

|                                           |                                        |
|-------------------------------------------|----------------------------------------|
| Operating voltage                         | max. 50 V AC/60 V DC                   |
| Operating voltage (only UL listed)        | max. 30 V AC/DC                        |
| Rated surge voltage                       | 1.5 kV                                 |
| Operating current per contact             | max. 4 A                               |
| Material group                            | IEC 60664-1, category I                |
| Locking of ports                          | M8 Snap In                             |
| Protection                                | IP65 inserted and tightened (EN 60529) |
| Material                                  | PUR                                    |
| suitable for corrugated tube (internal Ø) | 6.5 mm                                 |

#### Commercial data

country of origin DE

customs tariff number 85444290

Packaging unit 1

Sketch

Male



Product may differ from Image