

**M8 FEMALE 0° , SHIELDED**

PVC 3X0.34 shielded GRAY, UL,CSA 7.5m

Female straight

M8, 3-pole


shielded

with cable sleeves

Further cable lengths on request.

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

**Illustration**

Product may differ from Image

**Approvals**

\* only for products with UL/CSA approved cable

cCSAus

**Form**

Form 08741

**General data**

|                   |                                          |
|-------------------|------------------------------------------|
| Standards         | DIN EN 61076-2-104 (M8)                  |
| Temperature range | -25...+85 °C, depending on cable quality |

**Cables**

|                            |                               |
|----------------------------|-------------------------------|
| No./diameter of wires      | 3 x 0.34 mm <sup>2</sup>      |
| Wire isolation             | PVC (br, bl, bk)              |
| Material (jacket)          | PVC (UL/CSA)                  |
| Outer Ø                    | 5.0 mm ±5%                    |
| Temperature range (fixed)  | -30...+80 °C                  |
| Temperature range (mobile) | -5...+80 °C                   |
| Cable identification       | 200                           |
| Cable Type                 | 1 (PVC)                       |
| Approval (cable)           | UL (AWM-Style 2464/1731), CSA |
| Cable weight [g/m]         | 52,80                         |
| Material (wire)            | Cu wire, bare                 |
| Resistor (core)            | max. 57 Ω/km (20 °C)          |

|                                    |                                                |
|------------------------------------|------------------------------------------------|
| Single wire Ø (core)               | 0.15 mm                                        |
| Construction (core)                | 19× 0.15 mm (multi-strand wire class 5)        |
| Diameter (core)                    | 3× 0.34 mm <sup>2</sup>                        |
| AWG                                | similar to AWG 22                              |
| Material (wire isolation)          | PVC                                            |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (wire isolation)    | 45 ±5 D                                        |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                    |
| Color/numbering of wires           | br, bk, bl                                     |
| Stranding combination              | 3 wires twisted                                |
| Shield                             | yes                                            |
| Material (jacket)                  | PVC                                            |
| Material property (jacket)         | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (jacket)            | 85 ±5 A                                        |
| Outer-Ø (jacket)                   | 5.0 mm ±5%                                     |
| Color (jacket)                     | gray                                           |
| chemical resistance                | good resistance to oil, gasoline and chemicals |
| thermal resistance                 | flame retardant UL 1581 VW1 / CSA FT1          |
| Nominal voltage                    | 300 V AC                                       |
| Test voltage                       | 2000 V AC                                      |
| Current load capacity              | to DIN VDE 0298-4                              |
| Temperature range (fixed)          | -30...+80 °C                                   |
| Temperature range (mobile)         | -5...+80 °C                                    |
| Bend radius (fixed)                | 10× outer Ø                                    |
| Jacket Color                       | gray                                           |


**Technical Data**

|                               |                                                                 |
|-------------------------------|-----------------------------------------------------------------|
| Operating voltage             | max. 50 V AC/60 V DC                                            |
| Rated surge voltage           | 1.5 kV                                                          |
| Operating current per contact | max. 4 A                                                        |
| Locking of ports              | Screw thread (M8×1 mm) recommended torque 0.4 Nm, self-securing |
| Compression gland             | M8 (SW9)                                                        |
| Protection                    | IP65, IP66K, IP67 inserted and tightened (EN 60529)             |


**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879422017 |
| eClass                | 27279218      |
| Packaging unit        | 1             |

**Sketch**



Female



Product may differ from Image