

**M8 FEMALE 90° SNAP-IN LED**

PUR 3x0.25 GRAY, 1.5m

Female 90°

M8 (Snap In), 3-pole


2× LED (PNP), (NPN) on request

with cable sleeves

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

**Illustration**

Product may differ from Image

**Approvals**

cCSAus

\* only for products with UL/CSA approved cable

**Form**

Form 08281

**General data**

|                           |                                          |
|---------------------------|------------------------------------------|
| Standards                 | DIN EN 61076-2-104 (M8)                  |
| Pollution Degree          | 3                                        |
| Stripping length (jacket) | 20 mm                                    |
| Temperature range         | -25...+85 °C, depending on cable quality |

**Cables**

|                            |                                            |
|----------------------------|--------------------------------------------|
| No./diameter of wires      | 3× 0.25 mm <sup>2</sup>                    |
| Wire isolation             | PVC (br, bl, bk)                           |
| C-track properties         | 2 Mio.                                     |
| Material (jacket)          | PUR/PVC (UL/CSA)                           |
| Outer Ø                    | 4.5 mm ±5%                                 |
| Bend radius (moving)       | 15× outer Ø                                |
| Temperature range (fixed)  | -30...+80 °C                               |
| Temperature range (mobile) | -5...+80 °C                                |
| Cable identification       | 220                                        |
| Cable Type                 | 2 (PUR/PVC)                                |
| Approval (cable)           | UL (AWM-Style 20549/1731), CSA; CE conform |
| Cable weight [g/m]         | 26,62                                      |
| Material (wire)            | Cu wire, bare                              |
| Resistor (core)            | max. 79 Ω/km (20 °C)                       |
| Single wire Ø (core)       | 0.1 mm                                     |
| Construction (core)        | 32× 0.1 mm (multi-strand wire class 6)     |

|                                    |                                                                                                                                                        |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Diameter (core)                    | 3 × 0.25 mm <sup>2</sup>                                                                                                                               |
| AWG                                | similar to AWG 24                                                                                                                                      |
| Material (wire isolation)          | PVC                                                                                                                                                    |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free                                                                                                                |
| Shore hardness (wire isolation)    | 43 ±5 D                                                                                                                                                |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires           | br, bk, bl                                                                                                                                             |
| Stranding combination              | 3 wires twisted                                                                                                                                        |
| Shield                             | no                                                                                                                                                     |
| Material (jacket)                  | PUR                                                                                                                                                    |
| Material property (jacket)         | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 85 ±5 A                                                                                                                                                |
| Outer-Ø (jacket)                   | 4.5 mm ±5%                                                                                                                                             |
| Color (jacket)                     | gray                                                                                                                                                   |
| chemical resistance                | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                    | UL 300 V AC                                                                                                                                            |
| Test voltage                       | 2000 V AC                                                                                                                                              |
| Current load capacity              | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)          | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)         | -5...+80 °C                                                                                                                                            |
| Bend radius (fixed)                | 10× outer Ø                                                                                                                                            |
| Bend radius (moving)               | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track)    | max. 2 Mio. (25 °C)                                                                                                                                    |
| Traversing distance (C-track)      | max. 5 m (horizontal)                                                                                                                                  |
| Travel speed (C-track)             | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)             | max. 5 m/s <sup>2</sup>                                                                                                                                |
| Jacket Color                       | gray                                                                                                                                                   |



#### Technical Data

|                                           |                                        |
|-------------------------------------------|----------------------------------------|
| Operating voltage                         | 24 V DC ±25%                           |
| Operating voltage (only UL listed)        | max. 30 V DC                           |
| Rated surge voltage                       | 0.8 kV                                 |
| Operating current per contact             | max. 4 A                               |
| Material group                            | IEC 60664-1, category I                |
| LED display                               | yellow/green                           |
| Locking of ports                          | M8 Snap In                             |
| Protection                                | IP65 inserted and tightened (EN 60529) |
| Material                                  | PUR                                    |
| suitable for corrugated tube (internal Ø) | 6.5 mm                                 |


#### Commercial data

|                       |          |
|-----------------------|----------|
| country of origin     | DE       |
| customs tariff number | 85444290 |
| eClass                | 27061801 |
| Packaging unit        | 1        |

#### Sketch



Female



Product may differ from Image