


M12 female 0° with cable

PUR 4x0.34 gy UL/CSA+drag chain 20m

Female straight  
M12, 4-pole  
with cable sleeves  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

Link to Product

Illustration



Product may differ from image

Approvals



\* only for products with UL/CSA approved cable

cCSAus

Form

Form 222

General data

|                                    |                                                                                                                                            |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Standards                          | D N EN 6 076 2 0 (M 2)                                                                                                                     |
| Pollution Degree                   | 3                                                                                                                                          |
| Temperature range                  | 25 +85 °C depending on cable quality                                                                                                       |
| <b>Cables</b>                      |                                                                                                                                            |
| No /diameter of wires              | 4× 0.34 mm <sup>2</sup>                                                                                                                    |
| Wire isolation                     | PP (br wh bl bk)                                                                                                                           |
| C track properties                 | 0 Mio                                                                                                                                      |
| Material (jacket)                  | PUR (UL/CSA)                                                                                                                               |
| Outer Ø                            | 4.5 mm 5%                                                                                                                                  |
| Bend radius (moving)               | 0× outer Ø                                                                                                                                 |
| Temperature range (fixed)          | 40 +80 °C                                                                                                                                  |
| Temperature range (mobile)         | 25 +80 °C                                                                                                                                  |
| Cable identification               | 234                                                                                                                                        |
| Cable Type                         | 3 (PUR)                                                                                                                                    |
| Approval (cable)                   | cURus (AWM Style 20549/ 0493); CE conform                                                                                                  |
| Cable weight [g/m]                 | 36.30                                                                                                                                      |
| Material (wire)                    | Cu wire bare                                                                                                                               |
| Resistor (core)                    | max 57 Ω/km (20 °C)                                                                                                                        |
| Single wire Ø (core)               | 0 mm                                                                                                                                       |
| Construction (core)                | 42× 0 mm (multi strand wire class 6)                                                                                                       |
| Diameter (core)                    | 4× 0.34 mm <sup>2</sup>                                                                                                                    |
| AWG                                | similar to AWG 22                                                                                                                          |
| Material (wire isolation)          | PP                                                                                                                                         |
| Material property (wire isolation) | CFC halogen cadmium silicone and lead free                                                                                                 |
| Shore hardness (wire isolation)    | 70 5 D                                                                                                                                     |
| Wire Ø incl isolation              | 2.5 mm 5%                                                                                                                                  |
| Color/numbering of wires           | br bk bl wh                                                                                                                                |
| Stranding combination              | 4 wires twisted                                                                                                                            |
| Shield                             | no                                                                                                                                         |
| Material (jacket)                  | PUR                                                                                                                                        |
| Material property (jacket)         | CFC halogen cadmium silicone and lead free matt low adhesion machine easy to process abrasion resistant hydrolysis and microbial resistant |
| Shore hardness (jacket)            | 90 5 A                                                                                                                                     |
| Outer Ø (jacket)                   | 4.5 mm 5%                                                                                                                                  |
| Color (jacket)                     | gray                                                                                                                                       |
| chemical resistance                | good resistance to oil gasoline and chemicals (EN 608 404)                                                                                 |
| thermal resistance                 | flame retardant UL 58 VW / CSA FT / EC 60332 EC 60332 2 2                                                                                  |
| Nominal voltage                    | 300 V AC                                                                                                                                   |
| Test voltage                       | 2500 V AC                                                                                                                                  |
| Current load capacity              | to D N VDE 0298 4                                                                                                                          |
| Temperature range (fixed)          | 40 +80 °C (+90 °C at max 0 000 operating hours)                                                                                            |
| Temperature range (mobile)         | 25 +80 °C (+90 °C at max 0 000 operating hours)                                                                                            |
| Bend radius (fixed)                | 5× outer Ø                                                                                                                                 |
| Bend radius (moving)               | 0× outer Ø                                                                                                                                 |
| No. of bending cycles (C track)    | max 0 Mio (25 °C)                                                                                                                          |
| Travel speed (C track)             | max 3 m/s                                                                                                                                  |
| Acceleration (C track)             | max 0 m/s <sup>2</sup>                                                                                                                     |
| Torsion stress                     | 80°/m                                                                                                                                      |
| No. of torsion cycles              | max 2 Mio (25 °C)                                                                                                                          |

Torsion speed 35 cycles/min

Jacket Color gray

**Technical Data**

Operating voltage max 250 V AC/DC

Operating voltage (only UL listed) max 30 V AC/DC

Rated surge voltage 2.5 kV

Operating current per contact max 4 A

Material group EC 60664 category

Coding A coded

Locking of ports Screw thread (M 2× mm) recommended torque 0.6 Nm self securing

Compression gland M 2 (SW 3)

Protection P65 P66K P67 inserted and tightened (EN 60529)

Locking material Zinc die casting matte nickel plated

Material PUR

suitable for corrugated tube (internal Ø) 0 mm

**Commercial data**

country of origin DE

customs tariff number 85444290


EAN 40488792 260

eClass 272792 8

Packaging unit

**Sketch**

Female



Product may differ from image