

**M12 female 90° with cable LED**

PUR 4x0.34 bk UL/CSA 15m

Female 90°

M12, 4-pole


3× LED (PNP)

Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

**Illustration**

Product may differ from Image

**Approvals**

\* only for products with UL/CSA approved cable

cCSAus

**Form**

Form 12421

**Cables**

|                                    |                                            |
|------------------------------------|--------------------------------------------|
| No./diameter of wires              | 4 × 0.34 mm <sup>2</sup>                   |
| Wire isolation                     | PVC (br, wh, bl, bk)                       |
| C-track properties                 | 2 Mio.                                     |
| Material (jacket)                  | PUR/PVC (UL/CSA)                           |
| Outer Ø                            | 5.2 mm ±5%                                 |
| Bend radius (moving)               | 15× outer Ø                                |
| Temperature range (fixed)          | -30...+80 °C                               |
| Temperature range (mobile)         | -5...+80 °C                                |
| Cable identification               | 624                                        |
| Cable Type                         | 2 (PUR/PVC)                                |
| Approval (cable)                   | UL (AWM-Style 20549/1731), CSA; CE conform |
| Cable weight [g/m]                 | 42,68                                      |
| Material (wire)                    | Cu wire, bare                              |
| Resistor (core)                    | max. 57 Ω/km (20 °C)                       |
| Single wire Ø (core)               | 0.1 mm                                     |
| Construction (core)                | 42× 0.1 mm (multi-strand wire class 6)     |
| Diameter (core)                    | 4 × 0.34 mm <sup>2</sup>                   |
| AWG                                | similar to AWG 22                          |
| Material (wire isolation)          | PVC                                        |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free    |
| Shore hardness (wire isolation)    | 43 ±5 D                                    |

|                                 |                                                                                                                                                        |
|---------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wire-Ø incl. isolation          | 1.25 mm ±5%                                                                                                                                            |
| Color/numbering of wires        | br, bk, bl, wh                                                                                                                                         |
| Stranding combination           | 4 wires twisted                                                                                                                                        |
| Shield                          | no                                                                                                                                                     |
| Material (jacket)               | PUR/PVC                                                                                                                                                |
| Material property (jacket)      | CFC-, halogen-, cadmium-, silicone- and lead-free, matt, low-adhesion, machine easy to process, abrasion-resistant, hydrolysis and microbial resistant |
| Shore hardness (jacket)         | 80 ±5 A (PVC-under jacket); 85 ±5 A (PUR-jacket)                                                                                                       |
| Outer-Ø (jacket)                | 5.2 mm ±5%                                                                                                                                             |
| Color (jacket)                  | black                                                                                                                                                  |
| chemical resistance             | good resistance to oil, gasoline and chemicals                                                                                                         |
| Nominal voltage                 | UL 300 V AC                                                                                                                                            |
| Test voltage                    | 2000 V AC                                                                                                                                              |
| Current load capacity           | to DIN VDE 0298-4                                                                                                                                      |
| Temperature range (fixed)       | -30...+80 °C                                                                                                                                           |
| Temperature range (mobile)      | -5...+80 °C                                                                                                                                            |
| Bend radius (fixed)             | 10× outer Ø                                                                                                                                            |
| Bend radius (moving)            | 15× outer Ø                                                                                                                                            |
| No. of bending cycles (C-track) | max. 2 Mio. (25 °C)                                                                                                                                    |
| Traversing distance (C-track)   | max. 5 m (horizontal)                                                                                                                                  |
| Travel speed (C-track)          | max. 3.3 m/s                                                                                                                                           |
| Acceleration (C-track)          | max. 5 m/s²                                                                                                                                            |
| Jacket Color                    | black                                                                                                                                                  |

**Technical Data**

|                                           |                                                                    |
|-------------------------------------------|--------------------------------------------------------------------|
| Operating voltage                         | 24 V DC ±25%                                                       |
| Operating voltage (only UL listed)        | max. 30 V DC                                                       |
| Operating current per contact             | max. 4 A                                                           |
| Rated surge voltage                       | 0.8 kV                                                             |
| Material group                            | IEC 60664-1, category I                                            |
| Coding                                    | A-coded                                                            |
| LED display                               | LED (green): Power / LED (yellow): (S1) / LED (white): Signal (S2) |
| Locking of ports                          | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing   |
| Compression gland                         | M12 (SW13)                                                         |
| Protection                                | IP65, IP66K, IP67 inserted and tightened (EN 60529)                |
| Locking material                          | Zinc die casting, matte nickel plated                              |
| Material                                  | PUR                                                                |
| suitable for corrugated tube (internal Ø) | 10 mm                                                              |



**General data**

|                   |                                          |
|-------------------|------------------------------------------|
| Standards         | DIN EN 61076-2-101 (M12)                 |
| Pollution Degree  | 3                                        |
| Temperature range | -25...+85 °C, depending on cable quality |


**Commercial data**

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444290      |
| EAN                   | 4048879202657 |
| eClass                | 27279218      |
| Packaging unit        | 1             |

**Sketch**



Female



Product may differ from Image