

**M12 female receptacle A-cod. with cable rear mount**

PVC 5x0.34 gy UL/CSA 2m

Flange female

M12, 5-pole




Rear mounting

Further cable lengths on request.

The resistance to aggressive media should be individually tested for your application. Further details on request.


**Illustration**

stay connected



(\* for cable type 126, 732, 219, 619, 729)

# Female



Product may differ from Image

Approvals



Form

Form 13627

Cables

|                                    |                                                                  |
|------------------------------------|------------------------------------------------------------------|
| No./diameter of wires              | 5 × 0.34 mm <sup>2</sup>                                         |
| Wire isolation                     | PVC (br, wh, bl, bk, gnye)                                       |
| Material (jacket)                  | PVC (UL/CSA)                                                     |
| Outer Ø                            | 5.2 mm ±5%                                                       |
| Bend radius (moving)               | 10 × outer Ø                                                     |
| Temperature range (fixed)          | -30...+80 °C                                                     |
| Temperature range (mobile)         | -5...+80 °C                                                      |
| Cable identification               | 215                                                              |
| Cable Type                         | 1 (PVC)                                                          |
| Approval (cable)                   | UL (AWM-Style 2464/1731), CSA                                    |
| Cable weight [g/m]                 | 48,40                                                            |
| Material (wire)                    | Cu wire, bare                                                    |
| Resistor (core)                    | max. 60 Ω/km (20 °C)                                             |
| Single wire Ø (core)               | 0.15 mm                                                          |
| Construction (core)                | 19 × 0.15 mm (multi-strand wire class 5)                         |
| Diameter (core)                    | 5 × 0.34 mm <sup>2</sup>                                         |
| AWG                                | similar to AWG 22                                                |
| Material (wire isolation)          | PVC                                                              |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free                          |
| Shore hardness (wire isolation)    | 45 ±5 D                                                          |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                                                      |
| Color/numbering of wires           | br, bk, bl, wh, gnye longitudinally striped                      |
| Stranding combination              | 5 wires twisted around central filler                            |
| Shield                             | no                                                               |
| Material (jacket)                  | PVC                                                              |
| Material property (jacket)         | CFC-, cadmium-, silicone- and lead-free                          |
| Shore hardness (jacket)            | 85 ±5 A                                                          |
| Outer-Ø (jacket)                   | 5.2 mm ±5%                                                       |
| Color (jacket)                     | gray                                                             |
| chemical resistance                | good resistance to oil, gasoline and chemicals                   |
| thermal resistance                 | flame retardant UL 1581 VW1 / CSA FT1                            |
| Nominal voltage                    | UL 300 V AC                                                      |
| Test voltage                       | 2000 V AC                                                        |
| Current load capacity              | to DIN VDE 0298-4                                                |
| Temperature range (fixed)          | -30...+80 °C                                                     |
| Temperature range (mobile)         | -5...+80 °C                                                      |
| Bend radius (fixed)                | 5 × outer Ø                                                      |
| Bend radius (moving)               | 10 × outer Ø                                                     |
| Jacket Color                       | gray                                                             |
| <b>Technical Data</b>              |                                                                  |
| Operating voltage                  | max. 125 V AC/DC                                                 |
| Rated surge voltage                | 1.5 kV                                                           |
| Operating current per contact      | max. 4 A                                                         |
| Material group                     | IEC 60664-1, category I                                          |
| No. of poles                       | 5                                                                |
| Coding                             | A-coded                                                          |
| LED display                        | no                                                               |
| Locking of ports                   | Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing |
| Compression gland                  | M12 (SW14)                                                       |
| Protection                         | IP67 inserted and tightened (EN 60529)                           |

|                            |                                          |
|----------------------------|------------------------------------------|
| Protection NEMA            | 3, 4, 6P (UL 50E)                        |
| Locking material           | Brass, nickel plated                     |
| <b>General data</b>        |                                          |
| Standards                  | DIN EN 61076-2-101 (M12)                 |
| Pollution Degree           | 3                                        |
| Material (contact)         | Copper alloy                             |
| Material (contact surface) | Au                                       |
| Material (gasket)          | FKM                                      |
| Stripping length (jacket)  | 20 mm                                    |
| Temperature range          | -25...+85 °C, depending on cable quality |
| <b>Commercial data</b>     |                                          |
| country of origin          | DE                                       |
| customs tariff number      | 85444290                                 |
| EAN                        | 4048879612104                            |
| eClass                     | 27279220                                 |
| Packaging unit             | 1                                        |